

# Filtered air outlet connection MFU

📌 Sectors

📌 Applications: **Mobile**

📌 Issues **Fumes**

COD: KITSCARICESTMFU



Lateral connection diam. 200 mm for hose to discharge filtered air outside from MFU purifiers all.

## Detailed description

With this hose connection, filtered air from MFU purifiers can be expelled into a flexible hose (to be purchased separately) so that it cannot be fed back into the room.


### Kit contents:

- side panel for hose connection diam. 200

### Optional/not included:

- flexible hose made of sturdy PVC reinforced with harmonic steel spiral diam. 200mm





**Kit contents:**

- side panel for hose connection diam. 200

**On request / not included**

- flexible hose made of sturdy reinforced PVC with harmonic steel spiral diameter 200 mm, 10 m pieces



## Dimensions

Code	Ø mm
KITSCARICESTMFU	200

## Technical Data

Code	Pipe diameter mm	Attachment
KITSCARICESTMFU	200	200 mm diameter



## Related products



### MFU-HCO fumes extractor

MFU21HCO0000000


MFUHCO high-performance mobile wheeled fume and exhalation extractor for professional use, with 2mt suction arm, HEPA H13 99.99% absolute filtration and activated carbon



### MFU-HW welding fume extractor with superflex arm

MFU21HWXF000000

Mobile extractors for welding fumes and micro-dust, high performance for professional use, with HEPA H13 99.99% absolute filtration



### MFU-HW welding fume extractor with red arm

MFU21HWR0000000

Mobile extractors for welding fumes and micro-dust, high performance for professional use, with HEPA H13 99.99% absolute filtration



### MFU-HWF23 welding fume extractor double arm 3m

MFU21HW32F00000

Mobile welding fume extractor with superflex double arm, with filtration efficiency H13 99.99%.

